

# Cam Grips GR-30, GR-2000

# For thin materials Easy to grip





#### OI \ 2000

e-mail: info@hans-schmidt.com

Internet: http://www.hans-schmidt.com

## **Feature**

- They are suitable for checking thin materials.
- Samples will be tied automatically when the samples are pulled. (Cam system)

Fax:

**Phone:** int. + 49 / (0)8638 / 9410-0

int. + 49 / (0)8638 / 4825



## **Applications**

- The cam grips are installed on the a force gauge for tension test of various test pieces.



## Note

- Particular materials and shape can not be used.
- Combining with a test stand, more stable measuring becomes possible.
- All information is subject to change without prior notice.



## Specifications

Model	GR-30	GR-2000
Туре	normal	high capacity
Capacity	500 N (50 kgf)	2000 N (200 kgf)
Mounting screw (S)	M6	M10
Weight	180 g	870 g
Dimension (LxWxH)	36 x 22 x 64mm	62 x 50 x 98.5 mm
Opening width (A)	2 mm	4 mm
Sample width	30 mm	50 mm
Recommended	PS/FB/DS2/ZTS/ZTA series	PSH/ZTS/ZTA series
force gauge	20 N - 500 N	up to 2000 N

# Dimensional drawing

